

HIGH REP RATE TRIGGER UNIT TRIGGER GENERATOR

//////	11	1 1 1	11111
	POWER	R SUPPLY STATUS	
CAUTION		ENABLE	POWER
4			
THIS EQUIPMENT PRODUCES LETHAL VOLTAGES	Ö	END OF CHARGE	4 MINUTE WARM-UP TIME REQUIRED AFTER POWER-UP
	Ö	SUMMARY FAULT	

Utilizing a pulse forming circuit, the high-PRF trigger generator provides an 18 kV trigger pulse (into 50 Ohms) at up to 1 kHz pulse repetition frequency (PRF) to a Marx Generator unit.


Specification	Value	
Peak pulsed output voltage	18 kV	
Output voltage risetime	30 ns	
Control interface	Handheld fiber-optic remote or Delay Generator	
Input wavelength (FO)	820 nm	
Input power	90-250 VAC, 47-63 Hz	
Line current	90-140 Hz: 12A 180-250 Hz: 6A	
Requirements	An optical 820 nm delay generator (e.g. Berkeley Nucleonics 575) is required to operate this trigger generator.	


LED indicators on the front panel notify users of trigger-circuit HVPS conditions. Additional front panel options include: diagnostics, thyratron HVPS analog out, Marx analog out (V), Marx current out, and Marx V peak. Signals can be monitored on any 1- $M\Omega$ oscilloscope channel or handheld DVM through front panel BNC jacks.


The unit also conditions and routes optical signals from a delay generator (BNC 575) to control the charge and inhibit cycles of the thyratron HVPS and Marx HVPS (typically Lambda 802L or 402L). This functionality allows pulse charging of both the thyratron and the Marx Generator. The pulse charging mode minimizes high-voltage DC degrading effects (e.g. corona) and provides a safer high-voltage environment by inhibiting the default state of all power supplies.





HIGH REP RATE TRIGGER UNIT TRIGGER GENERATOR











Design

- Brushed stainless steel construction
- EMI shielded
- · Standard mains input power
- Quick connect output cable